

Rittal – The System.

Faster – better – everywhere.



SK 3240.300 Blue e+ outlet filter

State: 2025-07-04 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3240.300 - Blue e+ outlet filter

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

| | |
|------------------------|---|
| Model No. | SK 3240.300 |
| Version | wall-mounted |
| Benefits | Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Tool-free mounting |
| Material | Plastic |
| Color | RAL 7035 |
| Supply includes | Outlet Filters Pleated filter |
| Mounting cut-out | Width of opening: 224 mm Cut-out height: 224 mm |
| Suitable for Model No. | SK 3240.7xx/3240.9xx/3241.7xx/3241.9xx |
| Dimensions | Width: 255 mm Height: 255 mm Depth: 45.2 mm |

Features

| | |
|--------------------------------------|--|
| Protection category NEMA | Type 12 with chopped fiber filter/pleated filter Type 3, 3R, 4, 4X with chopped fiber filter/pleated filter and hose-proof hood |
| Protection category IP to IEC 60 529 | IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood |
| Packaging unit | 1 pc(s). |
| Net weight | 0.4 |
| Gross weight | 0.67 |
| Customs tariff number | 39269097 |
| EAN | 4028177998360 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |

Approvals

| | |
|-----------|--|
| Approvals | UL + C-UL - FTTA UR + C-UR (recognized) |
|-----------|--|