
Rittal – The System.

Faster – better – everywhere.





SK 3240.300 Blue e+ outlet filter

State: 2025-11-14 (Source: rittal.com/ca-en)



SK 3240.300 - Blue e+ outlet filter

The outlet filter is used in conjunction with the associated filter fan to dissipate lost heat out of the enclosures, to ventilate the enclosure and to protect temperature-sensitive components. This is done via the direct supply of ambient air that must be below the permissible temperature inside the enclosure.







Features

Model No.	SK 3240.300
Version	wall-mounted
Benefits	Easy filter change thanks to a new opening mechanism on the
	louvre grille
	Faster assembly on the enclosure due to optimized snap hooks
	Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Outlet Filters
	Pleated filter
Mounting cut-out	Width of opening: 224 mm
	Cut-out height: 224 mm
Suitable for Model No.	SK 3240.7xx/3240.9xx/3241.7xx/3241.9xx
Dimensions	Width: 255 mm
	Height: 255 mm
	Depth: 45.2 mm

© Rittal 2025 2

Features

Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3, 3R, 4, 4X with chopped fiber filter/pleated filter and hose- proof hood
Protection category IP to IEC 60 529	IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat
027	IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.67
Customs tariff number	39269097
EAN	4028177998360
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA
	UR + C-UR (recognized)

© Rittal 2025 3