

Rittal – The System.

Faster – better – everywhere.



SK 3243.066

Chopped fiber filter mat

State: 2026-06-28 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3243.066 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

Model No.	SK 3243.066
Version	for EMC filter fans
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Copper/nickel/chrome-coated chemical fibers
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3243.6.. 3244.6.. 3245.6..
Dimensions	Width: 294 mm Height: 294 mm Depth: 17 mm
Filter class	to DIN EN 779: G3
Packaging unit	5 pc(s).
Net weight	0.14 kg
Gross weight	0.156 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Features

Product description

SK spare filter mats, for EMC-filter fans, for SK
3243.6../3244.6../3245.6., WHD: 294 x 294 x 17 mm

Approvals

Approvals

CSA
UR + C-UR (recognized)