

Rittal – The System.

Faster – better – everywhere.



SK 3243.600

TopTherm Filter Fan Units

State: 2026-05-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3243.600 - TopTherm Filter Fan Units EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.



Features

Model No.	SK 3243.600
Version	wall-mounted EMC
Product description	EMC fan-and-filter units have a high screening/dampening effect and meet performance level 2 as per EN 61587-3.
Product changes	Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety.
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Diagonal, 1~ capacitor motor
Air throughput (unimpeded air flow)	At 50 Hz: 540 m ³ /h At 60 Hz: 590 m ³ /h
Air throughput with outlet filter incl. chopped fiber filter mat (quantity x order number)	1 x 3243060: 405/460 m ³ /h 2 x 3243060: 475/520 m ³ /h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.37 A At 60 Hz: 0.39 A

Features

Rated power Pel	At 50 Hz: 70 W At 60 Hz: 87 W
Dimensions	Width: 323 mm Height: 323 mm
Installation dimensions	Build depth: 25 mm Installation depth: 118.5 mm
Mounting cut-out	Width of opening: 292 mm Cut-out height: 292 mm
Note	To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
Protection category IP to IEC 60529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter Type 3 Type 3R Type 4 Type 4X with fleece filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Service life of fans (L10, 40 °C)	At 50 Hz: 65,000 h At 60 Hz: 61,000 h
Operating temperature range	-30 °C...55 °C
Storage temperature range	-30 °C...70 °C
Noise pressure level	At 50 Hz: 59 dB(A) At 60 Hz: 61 dB(A)
Packaging unit	1 pc(s).
Net weight	3.636 kg
Gross weight	3.836 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Features

Product description	SK Fan-and-filter unit TopTherm, 317.8/347.3 cfm 230 V, 1~, 50/60 Hz, WHD: 323 x 323 x 25 mm, EMC
---------------------	---

Approvals

Approvals	CSA 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---