


Rittal – The System.

Faster – better – everywhere.



SK 3285.940 Pleated filter

State: 2026-06-02 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3285.940 - Pleated filter for filter and roof-mounted fans, cooling units and chillers

Compared to conventional chopped fiber filters, the high-quality pleated filter technology enables a significant increase in the volume flow and thus an increase in the performance of the unit as well as a reduction in energy consumption. In addition, better filtration properties ensure less dust in the enclosure or unit, and the longer service life means significantly lower service costs.

Features

Model No.	SK 3285.940
Version	for chillers
Material	Polyester
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3319.100 / 3419.100 3320.200 / 3420.200 3334.300 / 3434.300 3334.360 / 3434.360 3334.440 / 3434.440 3334.460 / 3434.460 3334.470 / 3434.470 3334.480 / 3434.480 3334.400 / 3434.400 3334.450 / 3434.450
Dimensions	Width: 131 mm Height: 113 mm Depth: 13 mm
Filter class	to DIN EN 779: G3
Packaging unit	3 pc(s).
Net weight	0.087 kg
Gross weight	0.097 kg
Customs tariff number	56039390

Features

ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK Pleated filter for Blue e+ chiller (inverter housing) 3320.200/3334.300/3334.400, WHD: 131x113x13 mm
