

Rittal – The System.

Faster – better – everywhere.



SK 3311.040 Connection hose

State: 2025-08-02 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.040 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

Features

Model No.	SK 3311.040
Material	NBR (inner) with steel spiral and fabric insert
Version	Rack cooling
Length	1.8 m
Water connections	G 1½" internal thread
Operating temperature range	-30 °C...70 °C
Permissible operating pressure (p. max.)	16 bar
Packaging unit	2 pc(s).
Net weight	7.422
Gross weight	7.812
Customs tariff number	85444290
EAN	4028177663725
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712