

# Rittal – The System.

Faster – better – everywhere.



## SK 3314.635 Water module

State: 2026-06-29 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3314.635 - Water module for LCP Rear Door CW

Water module for individual output regulation or for determining the cooling output of an LCP Rear Door CW. Only suitable for use in conjunction with an active module. May be mounted either in the raised floor or above the rack, as preferred.

## Features

|                     |   |
|---------------------|---|
| Model No.           | SK 3314.635   |
| Version             | Room cooling<br>CW  |
| Benefits            | Individual output regulation measures the cooling output of each individual server rack   |
| Applications        | In conjunction with the passive and active modules of the LCP Rear Door CW portfolio  |
| Function principle  | Measurement of the inlet and return temperature, volumetric flow of the medium (water or water/glycol mixture), control valve actuator (PID)    |
| Material            | Carbon steel<br>Plastic<br>Brass<br>Copper  |
| Color               | Textured RAL 7035   |
| Note                | An active module is required for operation and electrical connection of the water module<br>The cable harness for the water module is 5 m long. |
| Dimensions          | Width: 340 mm<br>Height: 184 mm<br>Depth: 502 mm  |
| Cooling medium note | Saline and low-salinity water based on VDI 2035 plus max. 50 volume percent   |
| Water connections   | DN 25 (G 1" external thread)  |
| Rated voltage       | 24 V DC   |
| Rated output        | 0.01 kW   |

## Features

---

|  |   |
|--|---|
| Rated current                            | 0.4 A   |
| Operating temperature range              | 10 °C...50 °C   |
| Permissible operating pressure (p. max.) | 10 bar  |
| Water inlet temperature                  | 10 °C...30 °C   |
| Protection category IP to EN 60529       | IP 54   |
| Packaging unit                           | 1 pc(s).  |
| Net weight                               | 11 kg   |
| Gross weight                             | 11.9 kg   |
| Customs tariff number                    | 84199085  |
| Product description                      | SK Water module for LCP rear door CW for output regulation, WHD: 340x184x502 mm, RAL 7035 |

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UR + C-UR (recognized)    |
| Explanations | Declaration of conformity |