

Rittal – The System.

Faster – better – everywhere.



SK 3342.024

Rack-mounted fans for 482.6 mm (19")

State: 2025-09-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3342.024 - Rack-mounted fans for 482.6 mm (19") Air throughput 188.34 - 282..52 cfm

Rack-mounted fan for direct installation in the 19" level. Installation allows air to circulate permanently inside the enclosure, which prevents the creation of hot spots.

Features

Model No.	SK 3342.024
Product description	Rack-mounted fan for direct installation in the 19" level. The installation enables permanent air circulation in the enclosure, which prevents the creation of hot spots.
Color	RAL 7035
Supply includes	Wired unit ready for connection Incl. terminal strip and assembly components
Air throughput (unimpeded air flow)	480 m³/h
Note on Model No.:	Delivery times on request.
Rated operating voltage	24 V (DC)
Rated current max.	with DC: 0.74 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm
Distance between fan axes	105 mm
Number of fans	3
Noise pressure level	with DC: 51 dB(A)
Operating temperature range	-10 °C...55 °C
Packaging unit	1 pc(s).
Net weight	1.75
Gross weight	1.86

Features

Customs tariff number	84145915
EAN	4028177041509
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK