

Rittal – The System.

Faster – better – everywhere.



SV 3431.000

NH fuse-switch disconnecter, size 000

State: 2026-05-02 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3431.000 - NH fuse-switch disconnecter, size 000 for mounting plate assembly

Features

Model No.	SV 3431.000
Version	For mounting panel assembly.
Material	Fiberglass-reinforced polyamide Fire behavior corresponding to UL 94 Contact tracks: Silver-plated hard copper
Color	Chassis: RAL 9011 Cover: RAL 7035
Clamping area for laminated copper bars:	Clamping area width: 10 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	100 A
Rated operating voltage	690 V, 3~
For NH size	000
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 89 mm Height: 141.5 mm
Connection of round conductors	1.5 - 50 mm ²
Number of poles	3-pole
Round conductor cross-section	1.5 - 50 mm ²
Packaging unit	1 pc(s).
Net weight	0.401 kg

Features

Gross weight	0.453 kg
Copper weight (kg per piece)	0.15
Customs tariff number	85369095
ETIM 9	EC000249
ETIM 8	EC001040
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 000, 100 A, 690 V, 3-pole, box terminal, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK