

Rittal – The System.

Faster – better – everywhere.



IT 3659.181

Server telescopic slides

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 3659.181 - Server telescopic slides for IT enclosure systems and IT enclosures

Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.



Features

| | |
|-------------------------------------|--|
| Model No. | IT 3659.181 |
| Version | For level spacing of 470.65 - 599.65 mm |
| Product description | Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm. |
| Material | Carbon steel |
| Load capacity | 30 kg |
| Note | Only in conjunction with L-shaped profile rails |
| Suitable for | Enclosure type: TS TS IT VX VX IT Depth: = 600 mm |
| Packaging unit | 2 pc(s). |
| Net weight | 2.3 kg |
| Gross weight | 2.62 kg |
| PCF/VE (cradle-to-gate) | 5.1 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |

Features

| | |
|-----------------------|--|
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | Server telescopic rails for TS, TS IT, VX, VX IT, for depth 600 mm, extension: 490 mm, for server with maximum width of 430 mm |