

Rittal – The System.

Faster – better – everywhere.



IT 3659.191

Server telescopic slides

State: 2026-02-10 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

IT 3659.191 - Server telescopic slides for IT enclosure systems and IT enclosures

Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.



Features

Model No.	IT 3659.191
Version	For level spacing of 573.65 - 701.65 mm
Product description	Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.
Material	Carbon steel
Load capacity	30 kg
Note	Only in conjunction with L-shaped profile rails
Suitable for	Enclosure type: TS TS IT VX VX IT Depth: = 800 mm
Packaging unit	2 pc(s).
Net weight	2.82
Gross weight	3.08
PCF/VE (cradle-to-gate)	6 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

Customs tariff number 73269098

EAN 4028177964938

ETIM 9 EC002620

ETIM 8 EC002620

ECLASS 8.0 27189261