

Rittal – The System.

Faster – better – everywhere.



IT 3659.191

Server telescopic slides

State: 2026-06-19 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 3659.191 - Server telescopic slides for IT enclosure systems and IT enclosures

Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.



Features

Model No.	IT 3659.191
Version	For level spacing of 573.65 - 701.65 mm
Product description	Ensure optimum accessibility to the server, even when built-in. For servers with a max. width of 430 mm.
Material	Carbon steel
Load capacity	30 kg
Note	Only in conjunction with L-shaped profile rails
Suitable for	Enclosure type: TS TS IT VX VX IT Depth: = 800 mm
Packaging unit	2 pc(s).
Net weight	2.82 kg
Gross weight	3.08 kg
PCF/VE (cradle-to-gate)	6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	Server telescopic rails for TS, TS IT, VX, VX IT, for depth 800 mm, extension: 573 mm, for server with maximum width of 430 mm