

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.014 Hygienic Design

State: 2026-04-17 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.014 - Hygienic Design Compact enclosure HD, single-door

Enclosure solution tailored to the requirements of the food and beverage industry. Front roof tilted at 30 degrees. Sealing is clear from food due to blue coloring.

## Features

Model No.	HD 4000.014
Version	Roof slope 30° towards the front
Material	Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel HD lock inserts: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Supply includes	Housing of all-round solid construction Door with fitted seal Door hinged on the right, may be swapped to the left Mounting panel
Dimensions	Width: 760 mm Height, front: 810 mm Height rear: 981 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	705 mm x 735 mm
Door opening angle	125°
IK code	IK08
Base material	Stainless steel
Protection category IP to IEC 60529	IP 66 IP X9

# Features

---

Protection category NEMA	NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13
Type rating according to UL 50E	Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	44.8 kg
Gross weight	45.5 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
Product description	HD compact enclosure, 1.4301, WHD 760 x 810 x 300 mm

---