

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.240

## HD Leveling Feet

State: 2026-02-10 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# HD 4000.240 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

## Features

Model No.	HD 4000.240
Version	Without base mounting bracket
Benefits	<p>Minimizes cleaning time due to fully covered, permanently sealed threads</p> <p>Compensation of floor inclines up to an angle of 10° thanks to flexible base plate</p> <p>Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range</p> <p>Certification according to 3-A Sanitary standards</p>
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly components and seals
Load capacity	Max. 7000 N static per leveling foot
Dimensions	Thread: M12
Suitable for	Enclosure type: Compact enclosure HD VX VX SE TS
Leveling range	122 - 175 mm
Packaging unit	4 pc(s).
Net weight	2
Gross weight	2.342
Customs tariff number	73181900
EAN	4028177707641
ETIM 9	EC002622
ETIM 8	EC002622

# Features

---

ECLASS 8.0

27189263