## Rittal – The System.

Faster - better - everywhere.





# HD 4000.240 HD Leveling Feet

State: 2025-10-28 (Source: rittal.com/ca-en)



# HD 4000.240 - HD Leveling Feet

HD leveling feet to minimize cleaning time thanks to fully covered, permanently sealed thread. Also compensates for floor inclines of up to 10° thanks to the flexible base plate.

#### **Features**

Model No.	HD 4000.240
Version	Without base mounting bracket
Benefits	Minimizes cleaning time due to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base plate Leveling of bayed enclosures can be achieved on sloping floors, thanks to a large leveling range Certification according to 3-A Sanitary standards
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly components and seals
Load capacity	Max. 7000 N static per leveling foot
Dimensions	Thread: M12
Suitable for	Enclosure type: Compact enclosure HD VX VX SE TS
Leveling range	122 - 175 mm
Packaging unit	4 pc(s).
Net weight	2
Gross weight	2.342
Customs tariff number	73181900
EAN	4028177707641
ETIM 9	EC002622
ETIM 8	EC002622

© Rittal 2025 2

### Features

ECLASS 8.0

27189263

© Rittal 2025 3