## Rittal – The System.

Faster - better - everywhere.





# AS 4050.733 Wire end ferrule

State: 2025-11-28 (Source: rittal.com/ca-en)



## AS 4050.733 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.733	
Product description	With plastic collar.	
Technical specifications	Heat resistant up to 105 °C	
Material	E-Cu, tin-plated Plastic collar: Polypropylene	
Color	Black	
Length	8 mm	
AWG	16	
Internal diameter	3.5 mm	
For cross section	1.5 mm²	
DIN color code	Yes	
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.	
Standards	AEH DIN 46228	
Suitable for Model No.	4051.205 4051.210 4050.452	
Delivery form	Loose	
Packaging unit	500 pc(s).	
Net weight	0.5	
Gross weight	0.058	
Customs tariff number	85369010	
EAN	4028177805019	

© Rittal 2025

### **Features**

ETIM 9	EC000005	
ETIM 8	EC000005	
ECLASS 8.0	36659290	

## **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3