
## Rittal – The System.

Faster - better - everywhere.





# AS 4050.736 Wire end ferrule

State: 2025-11-17 (Source: rittal.com/ca-en)



## AS 4050.736 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.736
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Yellow
Length	12 mm
AWG	10
Internal diameter	6.3 mm
For cross section	6 mm²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	100 pc(s).
Net weight	0.1
Gross weight	0.1
Customs tariff number	85369010
EAN	4028177805040
ETIM 9	EC000005

© Rittal 2025

### Features

ETIM 8	EC000005
ECLASS 8.0	36659290

## **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3