Rittal – The System.

Faster - better - everywhere.





AS 4050.745 Wire end ferrule

State: 2025-11-06 (Source: rittal.com/ca-en)



AS 4050.745 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.745
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	8 mm
AWG	16
Internal diameter	4 mm
For cross section	1.5 mm²
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.5
Customs tariff number	85369010
EAN	4028177805132
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed) UR

© Rittal 2025

3