
# Rittal – The System.

Faster - better - everywhere.





# AS 4050.757 Wire end ferrule

State: 2025-10-31 (Source: rittal.com/ca-en)



## AS 4050.757 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.757
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Turquoise
Length	8 mm
AWG	22
Internal diameter	2 mm
Rittal color code	Yes
For cross section	0.34 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.  For tailored advice, please contact a Rittal representative.
 Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.026
Customs tariff number	85369010
EAN	4028177815797
ETIM 9	EC000005

© Rittal 2025 2

### Features

ECLASS 8.0 36659290

# **Approvals**

Approvals UL + C-UL (listed) UR

© Rittal 2025

3