Rittal – The System.

Faster - better - everywhere.





AS 4050.785 Wire end ferrule

State: 2025-11-25 (Source: rittal.com/ca-en)



AS 4050.785 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.785
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	12 mm
AWG	10
Internal diameter	6.3 mm
Rittal color code	Yes
For cross section	6 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	100 pc(s).
Net weight	0.1
Gross weight	0.04
Customs tariff number	85369010
EAN	4028177815681

© Rittal 2025 2

Features

ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3