

Rittal – The System.

Faster – better – everywhere.



AS 4050.785

Wire end ferrule

State: 2026-02-02 (Source: rittal.com/ca-en)

AS 4050.785 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.785
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	12 mm
AWG	10
Internal diameter	6.3 mm
Rittal color code	Yes
For cross section	6 mm ²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	100 pc(s).
Net weight	0.1
Gross weight	0.04
Customs tariff number	85369010
EAN	4028177815681
ETIM 9	EC000005

Features

ETIM 8 EC000005

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed)
UR