

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.574 Wire end ferrule

State: 2025-08-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.574 - Wire end ferrule Loose

With plastic collar.

## Features

Model No.	AS 4051.574
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Orange
Length	8 mm
AWG	20
Internal diameter	2.9 mm
Rittal color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999565
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

---

Approvals

UL + C-UL (listed)

UR