

Rittal – The System.

Faster – better – everywhere.



AS 4051.597 Wire end ferrule

State: 2026-03-28 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.597 - Wire end ferrule on belt

With plastic flange.

Features

| | |
|--------------------------|--|
| Model No. | AS 4051.597 |
| Product description | With plastic flange. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated Plastic collar: Polypropylene |
| Color | Orange |
| Length | 8 mm |
| AWG | 20 |
| Internal diameter | 2.6 mm |
| Rittal color code | Yes |
| For cross section | 0.5 mm ² |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Standards | AEH DIN 46228 |
| Delivery form | Taped |
| Packaging unit | 5,000 pc(s). |
| Net weight | 5 kg |
| Gross weight | 0.536 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Features

| | |
|---------------------|---|
| Product description | Wire end ferrules for crimping machines, 0.5 mm ² , AWG 20, 8 mm, orange, on belt, 5000 pc(s). |
|---------------------|---|

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|