

Rittal – The System.

Faster – better – everywhere.



AS 4051.598 Wire end ferrule

State: 2025-12-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.598 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.598
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Orange
Length	10 mm
AWG	20
Internal diameter	2.6 mm
Rittal color code	Yes
For cross section	0.5 mm ²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5
Gross weight	0.589
Customs tariff number	85369010
EAN	4028177938663
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals

UL + C-UL (listed)