


Rittal – The System.

Faster – better – everywhere.



AS 4051.638 Wire end ferrule

State: 2025-12-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.638 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4051.638
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	10 mm
AWG	20
Internal diameter	2.6 mm
For cross section	0.5 mm ²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210
Delivery form	Loose (10 packs of 100)
Packaging unit	1,000 pc(s).
Net weight	1
Gross weight	0.094
Customs tariff number	85369010
EAN	4028177815865
ETIM 9	EC000005

Features

ETIM 8	EC000005
ECLASS 8.0	36659290

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------