

Rittal – The System.

Faster – better – everywhere.



AS 4054.021 Crimping pliers

State: 2026-04-18 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.021 - Crimping pliers For cable lugs

For use with non-insulated ring terminals



Features

Model No.	AS 4054.021
Version	Angled
Product description	For crimping non-insulated ring terminals.
Benefits	Unlockable forced lock Thanks to optimized lever transmission, only minimal actuation forces are required even for larger cross-sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Indent crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 10
For cross section	0.35 - 6 mm ²
Packaging unit	1 pc(s).
Net weight	0.425 kg
Gross weight	0.435 kg
Customs tariff number	82032000

Features

ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping plier 0.5 - 6 mm ² , indent-C.
