

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.024 Crimping pliers

State: 2025-08-29 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.024 - Crimping pliers For cable lugs

For use with non-insulated ring terminals



## Features

Model No.	AS 4054.024
Version	Straight
Product description	For crimping non-insulated ring terminals.
Benefits	Unlockable forced lock Thanks to optimized lever transmission, only minimal actuation forces are required even for larger cross-sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Indent crimp
Dimensions	Height: 68 mm Length: 256 mm
AWG	8 - 4
For cross section	10 - 25 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	0.52
Gross weight	0.67
Customs tariff number	82032000

# Features

EAN	4028177807655
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811