


Rittal – The System.

Faster – better – everywhere.



AS 4054.140 Crimper

State: 2025-12-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.140 - Crimper For cable lugs

For use with insulated ring terminals and connectors



Features

Model No.	AS 4054.140
Version	Angled
Product description	For crimping insulated ring terminals and connectors.
Benefits	Clear assignment of cross section through color coding on the dies Unlockable forced lock Releases as soon as the required pressure is reached, to prevent ramming
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Oval crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 14
For cross section	0.75 - 2.5 mm ²
Packaging unit	1 pc(s).
Net weight	0.42
Gross weight	0.44
Customs tariff number	82032000

Features

EAN	4028177807686
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811