

Rittal – The System.

Faster – better – everywhere.



AS 4055.020

Manual hydraulic punch

State: 2025-08-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.020 - Manual hydraulic punch

For punching round, square and rectangular cut-outs.



Features

Model No.	AS 4055.020
Version	Flexible, with hydraulic hose and separate cylinder
Product description	For punching round, square and rectangular openings.
Benefits	Extend tool life with a built-in pressure relief valve
Material	Aluminum
Supply includes	Manual hydraulic punch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5/19 mm HSS pilot drill Ø 11 mm Spacer bushing set (3-part) Plastic case
Hydraulic operation	Round hole punch up to Ø 82 mm Rectangular hole punch up to 46 x 86 mm Punching force 75 kN Max. operating pressure 680 bar/9850 psi Square knockout punch up to 92 x 92 mm
Packaging unit	1 pc(s).
Net weight	3.4
Gross weight	3.546
Customs tariff number	84678900
EAN	4028177807921

Features

ETIM 9	EC001085
ETIM 8	EC001085
ECLASS 8.0	21049046