Rittal – The System.

Faster – better – everywhere.





AS 4055.020 Manual hydraulic punch

State: 2025-11-05 (Source: rittal.com/ca-en)



AS 4055.020 - Manual hydraulic punch

For punching round, square and rectangular cut-outs.



Features

| Model No. | AS 4055.020 | |
|-----------------------|--|--|
| Version | Flexible, with hydraulic hose and separate cylinder | |
| Product description | For punching round, square and rectangular openings. | |
| Benefits | Extend tool life with a built-in pressure relief valve | |
| Material | Aluminum | |
| Supply includes | Manual hydraulic punch | |
| | Hydraulic screw Ø 19 mm | |
| | Hydraulic screw Ø 9.5/19 mm | |
| | HSS pilot drill Ø 11 mm | |
| | Spacer bushing set (3-part) | |
| | Plastic case | |
| Hydraulic operation | Round hole punch up to Ø 82 mm | |
| | Rectangular hole punch up to 46 x 86 mm | |
| | Punching force 75 kN | |
| | Max. operating pressure 680 bar/9850 psi | |
| | Square knockout punch up to 92 x 92 mm | |
| Packaging unit | 1 pc(s). | |
| Net weight | 3.4 | |
| Gross weight | 3.546 | |
| Customs tariff number | 84678900 | |
| EAN | 4028177807921 | |
| | | |

© Rittal 2025

Features

| ETIM 9 | EC001085 | |
|------------|----------|--|
| ETIM 8 | EC001085 | |
| ECLASS 8.0 | 21049046 | |

© Rittal 2025 3