

Rittal – The System.

Faster – better – everywhere.



AS 4055.237

Hole punch, round

State: 2025-06-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.237 - Hole punch, round for carbon steel

For punching round cut-outs

Features

| | |
|--|--|
| Model No. | AS 4055.237 |
| Version | With 3 cutting tips |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | Die Stamp Tension screw without ball bearing |
| Workable material | Carbon steel |
| Max. material thickness that can be machined for sheet steel | 3 mm |
| Ø hole punch | 37 mm |
| Note | Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number | 4055.663 |
| Tension screw (Ø x L) | 19 x 55 mm |
| Hydraulic tension screw Ø | 19 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.453 |
| Gross weight | 0.487 |
| Customs tariff number | 82073010 |
| EAN | 4028177808294 |
| ETIM 9 | EC000156 |
| ETIM 8 | EC000156 |

Features

ECLASS 8.0

21049047