

Rittal – The System.

Faster – better – everywhere.



SZ 4140.120 Compact light

State: 2025-12-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4140.120 - Compact light

Compact light – slimline, space-saving light for use inside the enclosure



Features

Model No.	SZ 4140.120
Benefits	<p>Slimmer: Height and depth reduced by around 50%, takes up 75% less volume than conventional lights</p> <p>Faster: Universal quick-release fastening at TS punchings using clips, screws or powerful magnets (optional). Easy to insert at the sides or rear, fit light and you're done!</p> <p>Door-operated switch connection can be made using 2-pole connector</p> <p>Transparent light cover, fluted on inside</p>
Color	Similar to RAL 7035
Supply includes	<p>Compact light with clip and screw mounting kits</p> <p>Light (bulb)</p> <p>Light cover</p> <p>Connection cable</p> <p>Assembly components</p>
Rated power	14 W
Length of connection cable	3 m

Features

Mounting distance screws	725 mm
Ballast	EB
Connection options	Integrated connection cable with open end Door-operated switch
Light (bulb)	T5 fluorescent lamp
Protection category	II (total insulation)
Switch (type)	Integrated, on/off/door-operated switch
Cable deflection via rear possible	Yes
Light cover	Yes
Light – installation type	Screw fastening Clip fastening Magnetic fastener (accessories)
Rated impulse withstand voltage, phase to earth	Depending on the power supply
Rated impulse withstand voltage, phase to phase	Depending on the power supply
Rated insulation voltage	Depending on the power supply
with DC	0.57 A
Mounting distance clip/magnet	650 mm
Installation options	TS horizontal profile from roof frames: direct TS, SE vertical profile, direct SE profiles to the front and rear of roof frames: direct SE profiles to the side of roof frames: direct AE, CM, TP: with magnet mounting kit AE: with rail for interior installation
Note	Door-operated switch connection can be made using 2-pole connector
Note on Model No.:	Cable deflector across rear possible
Dimensions	Width: 705 mm Height: 59 mm Depth: 24 mm

Features

Operating temperature range	-15 °C...45 °C
Storage temperature range	-20 °C...70 °C
Rated operating voltage	24 V (DC)
Protection category IP to IEC 60529	IP 20
Packaging unit	1 pc(s).
Net weight	0.739
Gross weight	0.74
Customs tariff number	94054990
EAN	4028177550308
E-Number Sweden	E4302503
ECLASS 8.0	27189241