
Rittal – The System.

Faster – better – everywhere.





SZ 4169.000 Punched Rails, 23 x 23 mm

State: 2025-10-27 (Source: rittal.com/ca-en)



SZ 4169.000 - Punched Rails, 23 x 23 mm for VX, TS, VX SE

Mounted on the horizontal and vertical enclosure sections using additional assembly components.







2

Features

Model No.	SZ 4169.000
Material	Carbon steel
Surface finish	Zinc-plated
Length	295 mm
Installation options	In VX on vertical and horizontal enclosure section via TS mounting brackets.
	In VX SE on vertical enclosure section via mounting brackets in conjunction with adapter rail VX
	In VX SE on the horizontal profile/in the roof via mounting brackets in conjunction with adapter rail VX in depth
	On the vertical enclosure section: Directly via support brackets TS, via adapter rail for PS compatibility in conjunction with angle
	brackets, mounting brackets or support brackets PS.
	On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS
Suitable for	Enclosure type: VX
	TS
	VX SE
	Suitable for width or height or depth: 400 mm
Packaging unit	12 pc(s).

© Rittal 2025

Features

Net weight	2.052
Gross weight	2.22
PCF/VE (cradle-to-gate)	8.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177093102
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234

© Rittal 2025 3