

Rittal – The System.

Faster – better – everywhere.



SZ 4173.000

Punched Rails, 23 x 23 mm

State: 2026-04-15 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4173.000 - Punched Rails, 23 x 23 mm for VX, TS, VX SE

Mounted on the horizontal and vertical enclosure sections using additional assembly components.



Features

Model No.	SZ 4173.000
Material	Carbon steel
Surface finish	Zinc-plated
Length	895 mm
Installation options	<p>In VX on vertical and horizontal enclosure section via TS mounting brackets.</p> <p>In VX SE on vertical enclosure section via mounting brackets in conjunction with adapter rail VX</p> <p>In VX SE on the horizontal profile/in the roof via mounting brackets in conjunction with adapter rail VX in depth</p> <p>On the vertical enclosure section: Directly via support brackets TS, via adapter rail for PS compatibility in conjunction with angle brackets, mounting brackets or support brackets PS.</p> <p>On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS</p>
Suitable for	<p>Enclosure type: VX</p> <p>TS</p> <p>VX SE</p> <p>Suitable for width or height or depth: 1,000 mm</p>
Packaging unit	12 pc(s).

Features

Net weight	6.528 kg
Gross weight	6.871 kg
PCF/VE (cradle-to-gate)	26.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Product description	SZ Punched rail 23 x 23 mm, for TS, SE, for WHD: 1000 mm, L: 895 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------