
Rittal - The System.

Faster - better - everywhere.





SZ 4315.550 Door-Operated Switch

State: 2025-10-26 (Source: rittal.com/ca-en)



SZ 4315.550 - Door-Operated Switch

With mounting accessories, with or without connection cable.

Features

Model No.	SZ 4315.550
Version	With connection cable
Length	600 mm
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for standard and courtesy lights without an integrated door- operated switch
Dimensions	Length: 600 mm
Electrical connection	240 V AC/6 A 125 V DC/8 A 24 V AC/6 A 24 V DC/6 A
Rated operating voltage	400 V
Protection category IP to IEC 60 529	IP 40
Packaging unit	1 pc(s).
Net weight	0.115
Gross weight	0.122
Customs tariff number	85365019
EAN	4028177501461
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266

© Rittal 2025

Approvals

Approvals CQC

CQC-CCC

CSA

UL + C-UL (listed)

UR

© Rittal 2025 3