

Rittal – The System.

Faster – better – everywhere.



PS 4338.000 Cable clamp rail

State: 2026-05-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4338.000 - Cable clamp rail Mounting angle for TS, PC, TP universal console, TS base/plinths

For TS, PC, TP universal console, base/plinths, as strain relief for cable entries.

Features

Model No.	PS 4338.000
Product description	Provides strain relief for cable entries. Depth-variable mounting in 25 mm hole pattern on the horizontal enclosure profile or in the TS base/plinth/Flex-Block.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Mounting tip	When mounting on a TS base/plinth, the fastening bolt for bases/plinths is required
Dimensions	Length: 1,585 mm
Suitable for	Enclosure type: TS PC TP universal console Width: = 1,600 mm
Suitable for width	1,600 mm
Packaging unit	2 pc(s).
Net weight	8.664 kg
Gross weight	9.12 kg
Customs tariff number	73269098
ETIM 9	EC000322
ETIM 8	EC000322
ECLASS 8.0	27400604
Product description	SZ Cable clamp rail (right angle section), for TS, PC, TP universal console, TS base/plinth, Flex-Block, for W: 1600 mm