Rittal - The System.

Faster – better – everywhere.





DK 5501.480 Slide Rails, 1U, Depth-Variable

State: 2025-11-15 (Source: rittal.com/ca-en)



DK 5501.480 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .





Features

Model No.	DK 5501.480
Benefits	Tool-free, time-saving one-person assembly from the front of the enclosure
	All three mounting holes in the EIA system punchings are available for screw-fastening the equipment
	Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm
	(19") system punchings is also possible
Applications	For assembly on the front mounting level
	To support heavy installed equipment.
	To adapt to individual distances between 19" levels
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear
	482.6 mm (19") mounting frames, front and rear
	19" standard profile rails in VX IT
Load capacity	1500 N
Note	Effective contact surface 25 mm per side

© Rittal 2025

Features

Suitable for	Enclosure type: TS IT VX IT TE TY CobleMet
Distance between levels	TX CableNet 600 - 900 mm
Packaging unit	2 pc(s).
Net weight	3.2
Gross weight	3.74
Customs tariff number	73269098
EAN	4028177679030
E-Number Sweden	E7239697
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3