

Rittal – The System.

Faster – better – everywhere.



DK 5501.835

Air baffle plates for TS IT 19" profile frames

State: 2025-07-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.835 - Air baffle plates for TS IT 19" profile frames

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

Model No.	DK 5501.835
Product description	With all-round brush strip for partitioning without disruption when busbar systems are installed on the outer mounting level.
Applications	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material	Carbon steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly components 6 blanking panels, 1 U
Mounting tip	For partitioning, the vertical trim panels with brush strips can be mounted to both the front and rear 19" profile rails. The horizontal trim panels with brush strips can only be mounted on the front 19" profile rails.

Features

Suitable for	Width: 800 mm Height: 2,200 mm
Packaging unit	1 pc(s).
Net weight	8.74
Gross weight	9.2
Customs tariff number	73269098
EAN	4028177679207
E-Number Sweden	E7239701
ETIM 9	EC000331
ECLASS 8.0	27189272