
# Rittal - The System.

Faster - better - everywhere.





# DK 5502.010 Fan tray

State: 2025-11-20 (Source: rittal.com/ca-en)



## DK 5502.010 - Fan tray for VX IT, TS IT, TX CableNet

For active ventilation of the VX IT, TS IT, or TE 8000, depending on the version.

#### **Features**

Model No.	DK 5502.010
Product description	For active ventilation. The unit may optionally be extended with additional fans.
Applications	For use in the cut-out integrated into the roof plate
Color	RAL 7035
Supply includes	1 fan unit 2 fans 1 thermostat Connection cable, open-end Assembly components
Air throughput per fan (unimpeded air flow)	160/180
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 200 mm Height: 59 mm Depth: 550 mm
Air throughput of fans (unimpeded air flow)	1514
Installation options	In the VX IT with W x D (mm): 600 x 600/600 x 800/600 x 1000/600 x 1200/800 x 600 In TS IT with W x D: 600 x 600 / 600 x 800 / 600 x 1000 / 600 x 1200 / 800 x 600
Note	The specified sound level relates to the first fan  Connection via distributor box or country-specific connector
Sound pressure level per fan	37 dB(A)
Suitable for	Enclosure type: VX IT TS IT TX CableNet

© Rittal 2025

### **Features**

Operating temperature range	5 °C55 °C
Packaging unit	1 pc(s).
Net weight	3.027
Gross weight	3.3
Customs tariff number	84149000
EAN	4028177679245
ECLASS 8.0	27189272

## **Approvals**

© Rittal 2025 3