

Rittal – The System.

Faster – better – everywhere.



DK 5502.115 Cable finger

State: 2026-05-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.115 - Cable finger for VX IT

For U-based cable routing.

Features

| | |
|-----------------------|---|
| Model No. | DK 5502.115 |
| Version | for VX IT 19" standard profile rail |
| Product description | For structured cable routing on the 19" mounting level in 1 U increments. |
| Benefits | Simple, tool-free assembly by snap-mounting directly onto the 482.6 mm (19") profile rail |
| Material | Plastic to UL 94-V0 |
| Color | RAL 9005 |
| Installation options | Installation is possible both on the front and on the side of the profile rails at the front and rear |
| Note | Cable routing in conjunction with air baffle plates is supported |
| Dimensions | Width: 14 mm Length: 261 mm |
| Height units | 6 U |
| Packaging unit | 14 pc(s). |
| Net weight | 0.784 kg |
| Gross weight | 0.937 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400703 |
| Product description | DK Cable finger for TS-IT, 6 U, RAL 9005 |