

Rittal – The System.

Faster – better – everywhere.



DK 5502.115 Cable finger

State: 2025-12-08 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.115 - Cable finger for VX IT

For U-based cable routing.

Features

Model No.	DK 5502.115
Version	for VX IT 19" standard profile rail
Product description	For structured cable routing on the 19" mounting level in 1 U increments.
Benefits	Simple, tool-free assembly by snap-mounting directly onto the 482.6 mm (19") profile rail
Material	Plastic to UL 94-V0
Color	RAL 9005
Installation options	Installation is possible both on the front and on the side of the profile rails at the front and rear
Note	Cable routing in conjunction with air baffle plates is supported
Dimensions	Width: 14 mm Length: 261 mm
Height units	6 U
Packaging unit	14 pc(s).
Net weight	0.784
Gross weight	0.937
Customs tariff number	39269097
EAN	4028177679290
E-Number Sweden	E7239801
ETIM 9	EC000322
ECLASS 8.0	27400703