

Rittal – The System.

Faster – better – everywhere.



DK 5514.130

TS IT Network/Server Enclosure

State: 2026-04-04 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5514.130 - TS IT Network/Server Enclosure with glazed door, IP 55, with 19" profile rails

TS IT, sealed, for direct enclosure-specific climate control. 482.6 mm (19") interior installation with 482.6 mm (19") profile rails for a load capacity of up to 1,500 kg, available in a range of size variants, and with a protection category up to IP 55.

Features

Model No.	DK 5514.130
Material	Carbon steel Glazed aluminum door with 3 mm single-pane safety glass
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 7035
Color	Housing frame and panels: RAL 7035 Interior installation: RAL 9005
Supply includes	Enclosure frame TS 8 with doors and roof plate 12 x 19" fasteners 1 U, contacting (supplied) 50 multi-tooth screws, conductive (supplied loose) Glazed aluminum door, front, 180° hinges Carbon steel door at the rear, 180° hinges Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E Base tray with base plate, multi-piece, solid Roof plate, one-piece, solid
Dimensions	Width: 800 mm Height: 2,200 mm Depth: 1,000 mm
Height units	47 U
Height units	47 U
Distance between levels as delivered	745 mm

Features

Load capacity	15,000 N
Protection category IP to EN 60529	IP 55
Note on Model No.:	If used as a stand-alone installation, order the enclosure with the side panels already fitted and screw-fastened
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	126.7 kg
Gross weight	139 kg
Customs tariff number	94032080
ECLASS 8.0	27180207

Approvals

Certificates	Protection category
--------------	---------------------