

Rittal – The System.

Faster – better – everywhere.



SM 6002.130 Keyboard, pull-out

State: 2025-08-29 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 6002.130 - Keyboard, pull-out with integral trackball

Super-slimline keyboard with cursor keys and trackball, the handle also acts as a hand rest.



Features

Model No.	SM 6002.130
Product description	Super-slimline keyboard with cursor keys and trackball. The handle also acts as a hand rest. At a 10° angle for good ergonomics when typing.
Material	Carbon steel
Surface finish	Front panel: Powder-coated
Color	RAL 7035
Interfaces	2 x USB
Number keys	84
Installation options	in all sufficiently large surfaces (e.g. door, side panel) Front panels directly in the Comfort Panel or Optipanel with the appropriate size
Layout	German
Operating temperature range	5 °C...50 °C
Ambient humidity (non-condensing)	95 %
Storage temperature range	-10 °C...60 °C
Protection category IP to IEC 60529	IP 65 (at the front, sealed)
Packaging unit	1 pc(s).

Features

Net weight	4.722
Gross weight	4.922
PCF/VE (cradle-to-gate)	18.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84716060
EAN	4028177682122
ETIM 9	EC001692
ECLASS 8.0	19130490

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---