


Rittal – The System.

Faster – better – everywhere.



CP 6205.100 Mounting Bracket

State: 2025-08-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6205.100 - Mounting Bracket for interior fitting

To install system chassis and support strips horizontally and vertically. Comfort Panel from installation depth 74 mm or Optipanel from installation depth 100 mm. Using the mounting bracket in conjunction with the rail for interior installation, the system light LED can be mounted tool-free and without machining of the enclosure.



Features

Model No.	CP 6205.100
Product description	To install system chassis and support strips horizontally and vertically. Comfort Panel from installation depth 74 mm or Optipanel from installation depth 100 mm. Using the mounting bracket in conjunction with the rail for interior installation, the system light LED can be mounted tool-free and without machining of the housing.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	Comfort Panel from an installation depth of 74 mm Optipanel from an installation depth of 100 mm Rail for Interior Installation AX
Mounting tip	For installation in AX carbon steel, only in conjunction with rails interior installation AX
Packaging unit	4 pc(s).
Net weight	0.36
Gross weight	0.4
PCF/VE (cradle-to-gate)	1.4 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73182900
EAN	4028177536197
ETIM 9	EC002620
ECLASS 8.0	27189261