

Rittal – The System.

Faster – better – everywhere.



CP 6206.480

Connection console VESA 75/100

State: 2025-08-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.480 - Connection console VESA 75/100

For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75/100 connection. May be connected to Rittal CP 40 and CP 60 support arm systems, and also to CP 120 by using a Ø 130 mm to rectangular 120 x 65 mm support arm connection adaptor.



Features

Model No.	CP 6206.480
Version	Connection to Rittal support arm systems
Product description	For rear connection of flat operating housings, standard TFTs and industrial PCs with VESA 75/100 connection.
Benefits	<ul style="list-style-type: none">Fast, simple one-person assembly using machined keyholesMore space for installation and servicingCables may be routed to devices outside and below the consoleRemovable cover for easy cable routing and access to interior device connectionsIntegral cable clamping facilitiesCover and captive screws
Material	Die-cast zinc
Color	<ul style="list-style-type: none">Connection console: RAL 7035Cover: RAL 7024
Supply includes	<ul style="list-style-type: none">Seal and assembly componentsCable ties for cable clamping
Rifid y/n	Yes
Note	Depending on the application, an attachment, coupling or adapter are required
Load capacity	800 N

Features

Packaging unit	1 pc(s).
Net weight	2.5
Gross weight	2.775
Customs tariff number	85444290
EAN	4028177693920
ETIM 9	EC002622
ECLASS 8.0	27189263

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------