


# Rittal – The System.

Faster – better – everywhere.



## CP 6320.600

## Operating housing with handle strips

State: 2025-07-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6320.600 - Operating housing with handle strips

Command panel with handle strips in contemporary design of sheet steel, with Ø 130 mm support arm cut-out to fit CP 60/120/180 support arm system, service access optionally from the front or rear, aluminum front panel easily removable for machining, protection category IP 55



## Features

|                 |  |
|-----------------|--|
| Model No.       | CP 6320.600  |
| Material        | Housing and door: Carbon steel<br>Handle strips: Aluminum<br>Front panel: Aluminum<br>Cover caps: Plastic  |
| Surface finish  | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strip: Natural anodized<br>Front panel: Natural anodized.   |
| Color           | Housing and door: RAL 7035<br>Handle strip: Natural anodized<br>Front panel: Natural anodized.<br>Cover caps: Similar to RAL 7024  |
| Supply includes | Housing with cut-out and reinforcement for support arm connection Ø 130 mm<br>Front with maximum cut-out, covered with easily machinable 3 mm aluminum front panel<br>Side handle strips and cover caps<br>Cam lock with 3 mm double-bit insert<br>Integral interior mounting bracket with TS system punchings |

## Features

|                                     |  |
|-------------------------------------|--|
| Dimensions                          | Width: 600 mm<br>Height: 600 mm<br>Depth: 210 mm   |
| Protection category IP to IEC 60529 | IP 55  |
| Version                             | Service access from rear   |
| Note                                | The support arm connection and door catch may be swapped over by rotating the enclosure<br>Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out<br>Lock systems for servicing access from the rear: 27 mm lock inserts, type A, lock cylinder, plastic handles and T-handles, type B |
| Base material                       | Aluminum   |
| Lock                                | Lock version: Cam<br>No. of locks: 2<br>Lock Insert: 3 mm double-bit   |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 17.608   |
| Gross weight                        | 18.535   |
| EAN                                 | 4028177694019  |
| ECLASS 8.0                          | 27180505   |

## Approvals

|              |   |
|--------------|---|
| Approvals    | Bureau Veritas  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |