

Rittal – The System.

Faster – better – everywhere.



SM 6450.020

TFT monitor

State: 2026-02-11 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SM 6450.020 - TFT monitor

Mounting variant for surfaces and command panels.

Features

Model No.	SM 6450.020
Version	Without touchscreen
Product description	Mounting variant for surfaces and command panels.
Benefits	<p>High-quality industrial design</p> <p>Reduced installation work thanks to integral front frame</p> <p>No additional ventilation required</p> <p>Very small installation depth (45 mm)</p>
Material	Front frame: Aluminum
Surface finish	Powder-coated
Color	RAL 7035
Supply includes	<p>Seal</p> <p>Hex nuts (for installation in surfaces)</p> <p>VGA cable</p> <p>Threaded bolt M5, for rear mounting</p> <p>Touch variants additionally with integrated connection cable and CD-ROM driver</p> <p>With anti-reflection coated safety glass screen.</p>
Dimensions	<p>Width: 482.6 mm</p> <p>Height: 354.8 mm</p>
Interfaces	<p>VGA (D-SUB HD 15-pole)</p> <p>DVI-D</p>
Operating temperature range	0 °C...50 °C
Storage temperature range	-30 °C...85 °C
Note on Model No.:	Other variants as resistive touchscreen with serial or USB interface available on request.
Display brightness	350 cd/m ²
Contrast ratio	1000 : 1

Features

Diagonal	17"
Operating time	50,000 h
On Screen Display (OSD)	Operating buttons at the rear
Reading angle left/right	85 °
Display resolution	1280 x 1024 pixels
Rated power Pel	with DC: 20 W
H-Sync. (min./max.)	31.4 - 80 kHz
V-Sync. (min./max.)	60 - 75 Hz
Number of colors	16.7
Resolution of controller	VGA SVGA XGA SXGA
Packaging unit	1 pc(s).
Net weight	6.897
Gross weight	7.26
Customs tariff number	85286200
EAN	4028177442429
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

Explanations	Declaration of conformity
--------------	---------------------------