Rittal - The System.

Faster – better – everywhere.






CP 6538.010 Command panel housing with door

State: 2025-11-18 (Source: rittal.com/ca-en)




CP 6538.010 - Command panel housing with door Stainless steel

Operating door for enclosure made from stainless steel 1.4301, (AISI 304) with handle strips made from food-grade plastic. Can be combined with CP40 support arm system, stainless steel.







Features

CP 6538.010
With support arm connection CP 40, stainless steel
Housing and door: Stainless steel 1.4301 (AISI 304) Handle strips: Plastic approved for use with foodstuffs, dyed blue
Brushed, grain 400
Stainless steel
Handle strips: Similar to RAL 5002
Housing of all-round solid construction Cut-out and reinforcement for support arm system CP 40 stainless steel Fastener with guide plate Door with sealing frame and side handle strips Lock: 3 mm double-bit
Width: 400 mm Height: 400 mm Depth: 150 mm

© Rittal 2025

Features

Protection category IP to IEC 60 529	IP 66
Protection category NEMA	NEMA 12
Note	The support arm connection and door catch may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C
Base material	Stainless steel 1.4301 (AISI 304)
Note on Model No.:	Compatible mounting plate 5050.453 with shipping bag 5050.507
Packaging unit	1 pc(s).
Net weight	8.84
Gross weight	8.85
Customs tariff number	94032080
EAN	4028177220386
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3