Rittal - The System.

Faster – better – everywhere.





CX 6701.000 CX Pedestal

State: 2025-12-12 (Source: rittal.com/ca-en)



CX 6701.000 - CX Pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.







Features

Model No.	CX 6701.000
Version	Pedestal
Material	Housing: Carbon steel, 1.5 mm
	Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal
	Mounting plate: Carbon steel, 2.5 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing open at top
	Door or double door at front, with 3-point locking system
	Mounting panel
	Base Plates
	Lock: 3 mm double-bit
Dimensions	Width: 800 mm
	Height: 675 mm
	Depth: 400 mm

© Rittal 2025

Features

Dimensions of mounting plate (W x H)	720 mm x 625 mm
Number of doors	1
Door opening angle	130°
IK code	IK10
Note	To close the pedestal, a closure plate is required For a 2-piece console setup, a desk unit and a closure plate for the desk unit are required For a 3-piece console setup, a desk unit and console top-section are required
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Base material	Carbon steel
No. of locks	1
Lock version	3-point locking system
Lock Insert	3 mm double-bit
Lock	Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	38.5
Gross weight	39.875
Customs tariff number	94032080
EAN	4028177983793
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025