


Rittal – The System.

Faster – better – everywhere.



TP 6701.500 Pedestals

State: 2025-12-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6701.500 - Pedestals

Every TopConsole solution is based on four widths and two different depths.

Features

Model No.	TP 6701.500
Material	Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting panel: Carbon steel, 3.0 mm
Surface finish	dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing open at top Door, front Mounting panel Open base for individual cable entry
Dimensions of mounting plate (W x H)	699 mm x 625 mm
Number of doors	1
IK code	IK08
Base material	Carbon steel
Dimensions	Width: 800 mm Height: 675 mm Depth: 400 mm
Protection category IP to IEC 60529	IP 55 provided suitable base plates are selected
Protection category NEMA	NEMA 12 with selection of the appropriate base plate or trim panel
Packaging unit	1 pc(s).
Customs tariff number	94032080
EAN	4028177554085

Features

ECLASS 8.0	27180504
------------	----------

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
